

**Motic®**

MORE THAN MICROSCOPY

## MOTICAM S6

### USB CAMERAS

The new Motic sCMOS cameras developed by German engineering represent a new impetus to manufacturing quality, technical precision and lightweight design. With a member of this line the door for new application fields opens wide. The accelerated data readout (Rolling Shutter) also enables to work on fast moving phenomena.

The 6MP resolution of MotiCam S6 is clearly dedicated to large-sized displays and printing purposes. Presentations to a greater public through video projector, but also reports in hardcopy form are performed with ease of handling. Utilize an advanced technology for an affordable price.



[www.moticamseries.com](http://www.moticamseries.com) | [www.moticeurope.com](http://www.moticeurope.com)

## SCIENTIFIC CMOS CAMERA





## MOTICAM S6 TECHNICAL SPECIFICATIONS

<b>Sensor type</b>	sCMOS
<b>Sensor size</b>	1/1.8"
<b>Imaging area</b>	8.92mm (Diagonal)
<b>Capture resolution</b>	6MP
<b>Live display mode through USB</b>	3072x2048, 1536x1024 pixels
<b>Pixel size</b>	2.4x2.4µm
<b>Scan mode</b>	Progressive
<b>Shutter mode</b>	Rolling Shutter
<b>Data transfer</b>	USB 3.1
<b>Max. frames per second (fps*)</b>	3072x2048 @ 30fps 1536x1024 @ 50fps
<b>Exposure time</b>	16 µsec to 2 sec
<b>Operating temperature</b>	From -10 to +60 Degrees Celsius non condensing
<b>Sensitivity</b>	425mV(G) @ 1/30 sec
<b>Support device</b>	TWAIN, SDK and DirectShow Driver
<b>Supported OS</b>	Microsoft Windows 7/8/10, MAC OSX10.9, Linux or higher
<b>Minimum computer requirements</b>	2GHz dualcore - RAM memory 2GB - Video memory min. 512 MB
<b>Lens mount</b>	C-Mount
<b>Software</b>	Motic Images Plus 3.0 for Windows, OSX and Linux
<b>Functions</b>	Still image and video capture, live and still image measurement, image adjustments, white balance, automatic & manual exposure, individual objective calibration system.
<b>Power supply</b>	5V (from USB Port)
<b>Package includes</b>	CS ring adaptor, USB 3.1 cable, Motic 4-dot calibration slide, Motic Images Plus 3.0 for PC/OSX/Linux


*\*Frames per second under optimal lighting conditions and in compliance with computer technical requirements.*

### MOTIC IMAGES PLUS 3.0 IMAGE ANALYSIS SOFTWARE

Grab your image with highest sensor sensitivity. Navigate in the dark!

#### Motic Images Plus 3.0

By connecting your Moticam to your computer you will be able to work with our well-known software that comes included in the package. View, capture, edit, measure, make reports... all its standard features and the new ones packed in a new user-friendly interface.



FAST FRAME RATES



sCMOS SENSOR



USB 3.1 INTERFACE



MIP 3.0 SOFTWARE